

Lewatit® MonoPlus MP 800 is a strongly basic, macroporous anion exchange resin (type I) with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer, designed for all demineralization applications.

The monodisperse beads have high chemical and osmotic stability. The extremely high monodispersity (uniformity coefficient: max. 1.1) and very low fines content of max. 0.1 % (< 0.315 mm) result in particularly low pressure losses compared with standard resins. Due to its special macroporous structure

Lewatit® MonoPlus MP 800 stands for effective adsorption and desorption of naturally occurring organic substances.

Lewatit® MonoPlus MP 800 is especially applicable for:

- » the demineralization of water for industrial steam generation, e.g. Lewatit® WS System, Lewatit® Liftbed System or Lewatit® Rinsebed System
- » polishing using the Lewatit® Multistep System or a conventional mixed bed arrangement in combination with **Lewatit® MonoPlus SP 112 (H)**
- » condensate polishing in combination with **Lewatit® MonoPlus SP 112 (H)**

Lewatit® MonoPlus MP 800 adds special features to the resin bed:

- » high flow rates during regeneration and loading
- » a good utilization of the total capacity
- » low rinse water requirement
- » homogeneous throughput of regenerants, water and solutions, resulting in a homogeneous operating zone
- » virtually linear pressure drop gradient across the entire bed depth, allowing operation with higher bed depths
- » good separation of the components in mixed bed applications

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies (LPT).

General Description

Ionic form as shipped	Cl ⁻
Functional group	Quaternary amine, type I
Matrix	Crosslinked polystyrene
Structure	Macroporous
Appearance	Beige, opaque

Specified Data

	metric units	
Uniformity Coefficient	max.	1.1
Mean bead size	mm	0.62 (+/- 0.05)
Total capacity	min. eq/l	1.0

Physical and Chemical Properties

		metric units	
Bulk density	(+/- 5 %)	g/l	620
Density		approx. g/ml	1.06
Water retention		wt. %	63 - 68
Volume change	Cl ⁻ --> OH ⁻	max. vol. %	18
Stability	at pH-range		0 - 14
Storability	of the product	max. years	2
Storability	temperature range	°C	-20 - +40

This document contains important information and must be read in its entirety.

Recommended Operating Conditions*

		metric units	
OPERATION			
Operating temperature		max. °C	70
Operating pH-range			0 - 12
Bed depth		min. mm	800
Specific pressure drop	(15 °C)	approx. kPa*h/m ²	0.8
Pressure drop		max. kPa	300
Linear velocity	operation	max. m/h	60 - 100
REGENERATION, COUNTER-CURRENT			
Regenerant	type		NaOH
Regenerant	quantity	approx. g/l	50
Regenerant	concentration	approx. wt. %	2 - 4
Linear velocity		approx. m/h	5
Linear velocity	rinsing	approx. m/h	5
Rinse water requirement	slow / fast	approx. BV	2.5
REGENERATION, CO-CURRENT			
Regenerant	type		NaOH
Regenerant	quantity	approx. g/l	100
Regenerant	concentration	approx. wt. %	3 - 5
Linear velocity		approx. m/h	5
Linear velocity	backwash (20 °C)	approx. m/h	5
Linear velocity	rinsing	approx. m/h	5
Rinse water requirement	slow / fast	approx. BV	8
Bed expansion	(20 °C, per m/h)	approx. vol. %	18
Freeboard	backwash (extern / intern)	vol. %	100
OPERATION, MIXED BED			
Bed depth		min. mm	500
REGENERATION, MIXED BED			
Regenerant	type		NaOH
Regenerant	quantity	approx. g/l	100
Regenerant	concentration	approx. wt. %	2 - 6

* The recommended operating conditions refer to the use of the product under normal operating

This document contains important information
and must be read in its entirety.

PRODUCT INFORMATION LEWATIT® MonoPlus MP 800



conditions. It is based on tests in pilot plants and data obtained from industrial applications. However, additional data are needed to calculate the resin volumes required for ion exchange units. These data are to be found in our Technical Information Sheets.

*** 100m/h for polishing

This document contains important information
and must be read in its entirety.

Edition: 2014-01-16
Previous Edition: 2014-01-13

4/5

LANXESS
Energizing Chemistry

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

LANXESS Deutschland GmbH
BU LPT
D-51369 Leverkusen

www.lewatit.com
www.lanxess.com

This document contains important information
and must be read in its entirety.